## « A versatile Diamond Anvil Cell for X-ray inelastic, diffraction and

## imaging studies at synchrotron facilities»

## Sylvain Petitgirard <sup>a</sup>, Jeroen Jacobs <sup>b</sup>, Valerio Cerantola <sup>b</sup>, Chiara Cavallari <sup>b</sup>, Leonid

Dubrovinsky<sup>a</sup> and Christoph J. Sahle<sup>b</sup>

<sup>a</sup>Bayerisches Geoinstitut, University of Bayreuth, Bayreuth, D-95490, Germany

<sup>b</sup> European Synchrotron Radiation Facility, Grenoble, France

We present a new Diamond Anvil Cell design –hereafter called mBX110- that combines both the advantages of a membrane and screws to generate high pressure. It enables studies at large-scale facilities for most of synchrotron X-ray techniques and set-ups with the possibility to remotely control the pressure and the ease of use of the screws in the laboratory. It is fully compatible with various gas-loading systems as well as high/low temperature environments in the lab or at large scale facilities. The mBX110 posses an opening angle of 85 degrees suitable for single crystal diffraction and a large side opening of 110 degrees which can be used for X-ray inelastic techniques such as X-ray Raman scattering spectroscopy but also for X-ray emission, X-ray Fluorescence or X-ray absorption. An even larger opening of 150 degrees can be manufactured enabling X-ray tomography.



Figure 1: New Diamond Anvil Cell, mBX110, assembled and exploded view.